

Tabela de selecção: Sensores magnéticos

Distância de comutação

Actuadores magnéticos	BN 80-10Z	BN 80-01Z	BN 80-rz	BN 85-R	BN 310-10Z BN 310-01Z	BN 310-RZ	BN 32-10 BN 32-01 BN 32-11	BN 32-R BN 32-11R	BN 325-R	BN 65-10Z BN 65-10Z/1 BN 65-01Z	BN 65-RZ	BN 65-10Z/V BN 65-01Z/V	BN 65-RZ/V	BN 20-10Z BN 20-20Z BN 20-01Z BN 20-02Z BN 20-11Z	BN 20-RZ BN 20-2RZ BN 20-11RZ
BP 6 S			4-18	2-12											
BP 7 S			6-22												
BP 8	3-8	0-5													
BP 8 S				2-10											
BP 10	6-12	2-9	2-9		5		5			5					
BP 10 N						15		10	10		15				5
BP 10 S			10-30	5-20		15		10	10		15	5			5
2 x BP 10	12-20	2-13	2-13		17		12			17			3	12	
2 x BP 10 N						20		15	15		20				10
2 x BP 10 S			12-36	6-27		20		15	15		20	10			10
BP 15	8-14	2-10			6		6			6					
BP 15 N						17		12	12		17				7
BP 15 S			12-30	5-22		17		12	12		17	6			7
2 x BP 15	12-22	2-15			17		12			17					
2 x BP 15S			13-38	7-28											
2 x BP 15/2					17		12			17				12	
2 x BP 15/2 N						22		17	17		22				15
2 x BP 15/2 S						22		17	17		22				15
BP 34					5-20		15			15-20			15		
BP 34 N						15-30		10-25	10-25		15-30				10-25
BP 34 S			20-50	10-40		15-30		10-25	10-25		15-30	20			10-25
2 x BP 34	12-26	5-18													
2 x BP 34 S			22-60												
BP 20	12-24	0-14			20		15			20			10	15	
BP 20 N						3-25		5-20	5-20		25				15
BP 20 S			10-38	3-28		3-25		5-20	5-20		25	15			15
BP 31	12-24	0-14			20		15			20			10	15	
BP 31 N						3-25		5-20	5-20		25				15
BP 31 S			12-40	4-30		3-25		5-20	5-20		25	15			15
BP 11	22-28	2-16			8-20		5-15			20			15	15	
BP 11 N						15		10	10		15				5
BP 11 S			10-30	4-23		15		10	10		15	5			5
2 x BP 11 N						3-25		20	20		25				15
2 x BP 11 S						3-25		20	20		25	15			15
BP 12	24-32	4-20			10-30		10-25			10-30			20	25	
BP 12 N						20		15	15		20				10
2 x BP 12 N						10-30		10-25	10-25		10-30				5-20
2 x BP 12 S						10-30		10-25	10-25		10-30	25			5-20
BP 21					25-50		20-40			25-50			45	20-45	
BP 21 N						15-45		15-40	15-40		15-45				10-35
BP 21 S						15-45		15-40	15-40		15-45	30			10-35
2 x BP 21 N						20-60		20-55	20-55		20-60				15-50
2 x BP 21 S						20-60		20-55	20-55		20-60	20-55			15-50
BP 22 S												25			
BP 22 N+BP 22 S													35		
2 x BP 22 S												15-55			
BE 20					20		15						10	15	
BE 20 N						20		15	15		20				10
BE 20 S						20		15	15		20	6			10